

# HPX1-EHRN3R-GY3 Cut Sheet



IronHorse rotary handle, selector, black, external front mount, 2-position, lockable in ON-OFF, defeatable, NEMA 3R, IP65. For use with HMMP-32H manual motor protectors. 315mm shaft, operator and mounting screws included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HPX1-EHRN3R-GY3>

## Technical Specifications

<b>Brand</b>	IronHorse
<b>Item</b>	Handle
<b>Handle Type</b>	Rotary
<b>Handle Style</b>	Selector
<b>Color</b>	Black
<b>Mounting</b>	External front
<b>Number Of Positions</b>	2
<b>Lockable Positions</b>	ON-OFF
<b>Defeatable</b>	Yes
<b>NEMA Rating</b>	3R
<b>IP Rating</b>	IP65
<b>Test Function</b>	No
<b>For Use With</b>	HMMP-32H manual motor protectors
<b>Includes</b>	315mm shaft, operator and mounting screws

## Agency Approvals

<b>UL Listed File #</b>	E195426
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/HPX1-EHRN3R-GY3.pdf>  
See store item page for other formats.