

# HSST-3M2-RYG Cut Sheet



Patlite LED manual signal tower station kit, (3) tiers, 50mm diameter, red/amber/green, permanent light function, 100-240 VAC, clear lens, 271mm body length, off-white, 360 degree viewing angle, pole mount, IP20 and IP54.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HSST-3M2-RYG>

## Technical Specifications

Brand	Patlite
Item	Manual signal tower station kit
Bulb Type	LED
Number Of Tiers	3
Diameter	50mm
Light Color(s)	Red/amber/green
Light Function	Permanent
Voltage Rating	100-240 VAC
Lens Type	Clear
Body Length	271mm

Body Color	Off-white
Body Material	Polycarbonate
Tower Viewing Angle	360 degree
Connector Type	Pigtail
Mounting	Pole
IP Rating	IP20 and IP54
Kit Includes	(1) 3-tier signal tower, (1) 85mm mounting pole, (1) 285mm mounting pole, (1) 3-button switch box, (1) 4ft cable, (1) AC power adapter and mounting hardware

## Agency Approvals

UL Listed File #	E310210
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	NONE
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/HSST-3M2-RYG.pdf>  
See store item page for other formats.