

HUM-R-PT Cut Sheet



ProSense temperature/humidity sensor, room sensor, plastic wall mounting subplate process connection, Output: 2-channel, RTD/current, -19.9 to +60 °C, 0 to 99.9% RH, IP10, wall mount, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HUM-R-PT>

Technical Specifications

Brand	ProSense
Item	Temperature/humidity sensor
Sensor Type	Room sensor
Media Type	Air
Process Connection	Plastic wall mounting subplate
Number Of Output Channels	2
Output	RTD/current
Output	Pt100

Output 2	4–20 mA
Temperature Sensing Range	-19.9 to +60 °C
Humidity Sensing Range	0 to 99.9% RH
Operating Voltage	24 VDC
IP Rating	IP10
Housing Material	Plastic
Mounting	Wall
Electrical Connection	Screw terminals

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/HUM-R-PT.pdf>
See store item page for other formats.