

HW-J121005CHTLW Cut Sheet



Wiegmann JIC series enclosure, NEMA 1/3R/4X/6P/12, 12 x 10 x 5in (HxWxD), wall mount, fiberglass reinforced polyester, gray, single-door, (2) twist-lock latches, acrylic window.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HW-J121005CHTLW>

Technical Specifications

Brand	Wiegmann
Item	Enclosure
Series	JIC
Subpanel	Purchase subpanel separately
Slope Top	No
NEMA Rating	1/3R/4X/6P/12
Nominal Enclosure Height	12in
Nominal Enclosure Width	10in
Nominal Enclosure Depth	5in
Mounting	Wall
Integral Mounting Feet	No
Integral Mounting Flange	Yes

Dual Access	No
Knockouts	No
Material	Fiberglass reinforced polyester
Color	Gray
Cover Type	Single-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	(2) twist-lock latches
Window Material	Acrylic
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/HW-J121005CHTLW.pdf>
See store item page for other formats.