

# HW-N3R302412CH Cut Sheet



Wiegmann Control series enclosure, NEMA 1/3R, 30 x 24 x 12in (HxWxD), wall mount, fiberglass reinforced polyester, gray, single-door, (2) twist-lock latches, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HW-N3R302412CH>

## Technical Specifications

|                          |                              |
|--------------------------|------------------------------|
| Brand                    | Wiegmann                     |
| Item                     | Enclosure                    |
| Series                   | Control                      |
| Subpanel                 | Purchase subpanel separately |
| Slope Top                | No                           |
| NEMA Rating              | 1/3R                         |
| Nominal Enclosure Height | 30in                         |
| Nominal Enclosure Width  | 24in                         |
| Nominal Enclosure Depth  | 12in                         |
| Mounting                 | Wall                         |
| Integral Mounting Feet   | Yes                          |
| Integral Mounting Flange | No                           |

|                           |                                 |
|---------------------------|---------------------------------|
| Dual Access               | No                              |
| Knockouts                 | No                              |
| Material                  | Fiberglass reinforced polyester |
| Color                     | Gray                            |
| Cover Type                | Single-door                     |
| Hinge Type                | Continuous hinge                |
| Number of Hinges Per Door | 1                               |
| Latch Type                | (2) twist-lock latches          |
| Padlock Attachment Type   | Padlock hasp and staple         |
| Padlockable               | Yes                             |
| Keylocking                | No                              |

## Agency Approvals

|                      |                                        |
|----------------------|----------------------------------------|
| UL Listed File #     | E64791                                 |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/HW-N3R302412CH.pdf>  
See store item page for other formats.