

HW-N4X241210CHW Cut Sheet



Wiegmann Control series enclosure, NEMA 1/3/3R/4X/12, 24 x 12 x 10in (HxWxD), wall mount, fiberglass reinforced polyester, gray, single-door, (2) twist-lock latches, padlock hasp and staple, acrylic window.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HW-N4X241210CHW>

Technical Specifications

Brand	Wiegmann
Item	Enclosure
Series	Control
Subpanel	Purchase subpanel separately
Slope Top	No
NEMA Rating	1/3/3R/4X/12
Nominal Enclosure Height	24in
Nominal Enclosure Width	12in
Nominal Enclosure Depth	10in
Mounting	Wall
Integral Mounting Feet	Yes
Integral Mounting Flange	No

Dual Access	No
Knockouts	No
Material	Fiberglass reinforced polyester
Color	Gray
Cover Type	Single-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	(2) twist-lock latches
Padlock Attachment Type	Padlock hasp and staple
Window Material	Acrylic
Padlockable	Yes
Keylocking	No

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/HW-N4X241210CHW.pdf>
See store item page for other formats.