

# HW-RHJ80806CHQR Cut Sheet



Wiegmann JIC series enclosure, NEMA 1/3R/4X/6P/12, 8 x 8 x 6in (HxWxD), wall mount, fiberglass reinforced polyester, gray, raised single-door, (1) quick-release latch, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HW-RHJ80806CHQR>

## Technical Specifications

|                          |                              |
|--------------------------|------------------------------|
| Brand                    | Wiegmann                     |
| Item                     | Enclosure                    |
| Series                   | JIC                          |
| Subpanel                 | Purchase subpanel separately |
| Slope Top                | No                           |
| NEMA Rating              | 1/3R/4X/6P/12                |
| Nominal Enclosure Height | 8in                          |
| Nominal Enclosure Width  | 8in                          |
| Nominal Enclosure Depth  | 6in                          |
| Mounting                 | Wall                         |
| Integral Mounting Feet   | No                           |
| Integral Mounting Flange | Yes                          |

|                           |                                 |
|---------------------------|---------------------------------|
| Dual Access               | No                              |
| Knockouts                 | No                              |
| Material                  | Fiberglass reinforced polyester |
| Color                     | Gray                            |
| Cover Type                | Raised single-door              |
| Hinge Type                | Continuous hinge                |
| Number of Hinges Per Door | 1                               |
| Latch Type                | (1) quick-release latch         |
| Padlock Attachment Type   | Padlock hasp and staple         |
| Padlockable               | Yes                             |
| Keylocking                | No                              |

## Agency Approvals

|                      |                                        |
|----------------------|----------------------------------------|
| UL Listed File #     | E64791                                 |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/HW-RHJ80806CHQR.pdf>  
See store item page for other formats.