

HW-WHJ161406CHSC Cut Sheet



Wiegmann JIC series enclosure, NEMA 1/3R/4X/6P/12, 16 x 14 x 6in (HxWxD), wall mount, fiberglass reinforced polyester, white, hinged screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HW-WHJ161406CHSC>

Technical Specifications

| | |
|---------------------------------|------------------------------|
| Brand | Wiegmann |
| Item | Enclosure |
| Series | JIC |
| Subpanel | Purchase subpanel separately |
| Slope Top | No |
| NEMA Rating | 1/3R/4X/6P/12 |
| Nominal Enclosure Height | 16in |
| Nominal Enclosure Width | 14in |
| Nominal Enclosure Depth | 6in |
| Mounting | Wall |
| Integral Mounting Feet | No |

| | |
|----------------------------------|---------------------------------|
| Integral Mounting Flange | Yes |
| Dual Access | No |
| Knockouts | No |
| Material | Fiberglass reinforced polyester |
| Color | White |
| Cover Type | Hinged screw cover |
| Hinge Type | Continuous hinge |
| Number of Hinges Per Door | 1 |
| Padlockable | No |
| Keylocking | No |

Agency Approvals

| | |
|-----------------------------|----------------------------------------|
| UL Listed File # | E64791 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/HW-WHJ161406CHSC.pdf>
See store item page for other formats.