

# IHBAA-40W Cut Sheet



International Power regulated linear power supply, 5 VDC @ 3A/15W, 12 or 15 VDC @ 0.8A/12W and -5, -12 or -15 VDC @ 0.8A/12W, 120/240 VAC nominal input, 1-phase, open frame, aluminum housing, chassis mount, turret terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/IHBAA-40W>

## Technical Specifications

<b>Brand</b>	International Power
<b>Item</b>	Power supply
<b>Power Supply Type</b>	Regulated linear
<b>Efficiency</b>	45% @ 120 VAC
<b>Output Configuration</b>	Triple output
<b>Output</b>	5 VDC @ 3A/15W
<b>Output 2</b>	12 or 15 VDC @ 0.8A/12W
<b>Output 3</b>	-5, -12 or -15 VDC @ 0.8A/12W
<b>Input voltage range</b>	120/240 VAC
<b>Input Voltage Selection Type</b>	Jumper
<b>Number of Input Phases</b>	1
<b>Protection Type(s)</b>	<ul style="list-style-type: none"><li>• short circuit</li><li>• overload</li><li>• overvoltage</li></ul>

<b>Remote On/Off</b>	No
<b>Voltage Monitoring</b>	No
<b>Enclosure Type</b>	Open frame
<b>Housing Material</b>	Aluminum
<b>Mounting</b>	Chassis
<b>Connector Type</b>	Turret terminals
<b>NEC Class 2</b>	No
<b>Integrated UPS Battery Control</b>	No
<b>Operating Temperature</b>	0 to 50 deg C

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E133338
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	C22.2 No. 1950
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/IHBAA-40W.pdf>  
See store item page for other formats.