

# IP06G Cut Sheet



PBC IP series closed full ball recirculating bearing, steel, 3/8in inside diameter, 5/8in outside diameter, 7/8in overall length. For use with 3/8in diameter PBC shafts.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/IP06G>

## Technical Specifications

<b>Brand</b>	PBC
<b>Item</b>	Full ball recirculating bearing
<b>Series</b>	IP
<b>Bearing Type</b>	Closed
<b>Bearing Material</b>	Steel
<b>Bearing Inside Diameter</b>	3/8in
<b>Bearing Outside Diameter</b>	5/8in
<b>Overall Length</b>	7/8in
<b>Flanged</b>	No
<b>For Use With</b>	3/8in diameter PBC shafts

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/IP06G.pdf>  
See store item page for other formats.