

IP10G Cut Sheet



PBC IP series closed full ball recirculating bearing, steel, 5/8in inside diameter, 1-1/8in outside diameter, 1-1/2in overall length. For use with 5/8in diameter PBC shafts.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/IP10G>

Technical Specifications

Brand	PBC
Item	Full ball recirculating bearing
Series	IP
Bearing Type	Closed
Bearing Material	Steel
Bearing Inside Diameter	5/8in
Bearing Outside Diameter	1-1/8in
Overall Length	1-1/2in
Flanged	No
For Use With	5/8in diameter PBC shafts

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/IP10G.pdf>
See store item page for other formats.