

# IPBB-NA4-2D-1 Cut Sheet



Penn-Union pre-insulated power bar, double-sided entry, 2 ports, aluminum, 1/8in hex conductor bolt, 14-4 AWG, AL9CU.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/IPBB-NA4-2D-1>

## Technical Specifications

<b>Brand</b>	Penn-Union
<b>Item</b>	Power bar
<b>Power Bar Type</b>	Pre-insulated
<b>Entry Type</b>	Double-sided
<b>Number Of Conductor Ports</b>	2
<b>Material</b>	Aluminum
<b>Color</b>	Black

<b>Conductor Bolt Style</b>	1/8in hex
<b>Conductor Size</b>	14-4 AWG
<b>Conductor Material</b>	Copper or aluminum
<b>Voltage Rating</b>	600V
<b>Dual Rating</b>	AL9CU
<b>Includes</b>	Oxide inhibitor

## Agency Approvals

<b>UL Listed File #</b>	E12822
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/IPBB-NA4-2D-1.pdf>  
See store item page for other formats.