

# IPPN16G Cut Sheet



PBC IPP series single pillow block, full ball recirculating bearing, 2.63in overall length, steel, 1in inside diameter, aluminum housing. For use with 1in diameter PBC shafts.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/IPPN16G>

## Technical Specifications

<b>Brand</b>	PBC
<b>Item</b>	Single pillow block
<b>Series</b>	IPP
<b>Block Type</b>	Open type
<b>Overall Length</b>	2.63in
<b>Bearing Type</b>	Full ball recirculating bearing
<b>Bearing Material</b>	Steel
<b>Housing Fit</b>	Self-aligning
<b>Bearing Inside Diameter</b>	1in
<b>Housing Material</b>	Aluminum
<b>For Use With</b>	1in diameter PBC shafts

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/IPPN16G.pdf>  
See store item page for other formats.