


ISEUR1 Cut Sheet



Macromatic intrinsically safe relay, 35mm DIN rail mount, finger-safe, Discrete Input: 1-point, 10 VDC input voltage, 102-132 VAC or 10-125 VDC coil voltage, Discrete Output: 1-point, relay, SPST, 5A contact rating, (1) N.O., LED indicator(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ISEUR1>

Technical Specifications

Brand	Macromatic
Relay Type	Intrinsically safe
Item	Relay
Mounting	35mm DIN rail
Relay Housing Type	Finger-safe
Number of Discrete Input Points	1
Input Voltage	10 VDC
Coil Voltage	102-132 VAC or 10-125 VDC

Number of Discrete Output Points	1
Discrete Output Type	Relay
Relay Configuration	SPST
Contact Rating	5A
Output Type	(1) N.O.
Connector Type	Screw terminal(s)
Indicator	LED
Application	Hazardous location rated

Agency Approvals

UL Listed File #	E318075
UL Recognized File #	None
UL Hazardous File #	E318075
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/ISEUR1.pdf>
See store item page for other formats.