


J50MD-M Cut Sheet



NITRA pneumatic rotary actuator, double acting, size 50, 0 to 190 degrees, rubber bumpers, anodized aluminum body, 1/8in female NPT port(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/J50MD-M>

Technical Specifications

Brand	NITRA
Item	Rotary actuator
Working Fluid	Air or inert gas
Action Type	Double acting
Size	50
Adjustable Travel	0 to 190 degrees
Cushion Type	Rubber bumpers
Body Material	Anodized aluminum
Port Size	1/8in female NPT

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/J50MD-M.pdf>
See store item page for other formats.