

JIC040403 Cut Sheet



Wiegmann Handy series enclosure, NEMA 12/13, 4 x 4 x 3in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/JIC040403>

Technical Specifications

Brand	Wiegmann
Item	Enclosure
Series	Handy
Slope Top	No
NEMA Rating	12/13
Nominal Enclosure Height	4in
Nominal Enclosure Width	4in
Nominal Enclosure Depth	3in
Mounting	Wall
Integral Mounting Feet	No

Integral Mounting Flange	Yes
Dual Access	No
Knockouts	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Screw cover
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/JIC040403.pdf>
See store item page for other formats.