

K-SS-EX-208026 Cut Sheet



IDEM safety switch, tongue (key) interlock, hazardous location rated, 180-degree adjustable head, (2) N.C. safety output(s), (2) N.O. monitoring output(s), 58 x 104 x 37mm, 316 stainless steel body, 316 stainless steel head.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/K-SS-EX-208026>

Technical Specifications

Brand	IDEM
Item	Safety switch
Actuator Type	Tongue (key) interlock
Head Type	180-degree adjustable
Action	Slow action break before make
Safety Output Type	(2) N.C.
Monitoring Output Type	(2) N.O.
Housing Size	58 x 104 x 37mm
Body Material	316 stainless steel
Head Material	316 stainless steel
IP Rating	IP67 IP69K
Connection	Pigtail
Cable Length	9.8ft/3m
Includes	(1) tamper-proof T20 Torx bit

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/K-SS-EX-208026.pdf>
See store item page for other formats.