

KA06MD-M Cut Sheet



NITRA pneumatic gripper, angular, double acting, 6mm bore, 30 degrees open position, -10 degrees closed position, side mount grip, anodized aluminum body, M3 x 0.5 female ISO port(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KA06MD-M>

Technical Specifications

| | |
|--------------------------------|---------------------|
| Brand | NITRA |
| Item | Gripper |
| Working Fluid | Air or inert gas |
| Grip Type | Angular |
| Action Type | Double acting |
| Bore Diameter | 6mm |
| Open Position | 30 degrees |
| Closed Position | -10 degrees |
| Grip Mount Style | Side |
| Body Material | Anodized aluminum |
| Port Size | M3 x 0.5 female ISO |
| Cycle Rate | 180 cyc/min |
| Maximum Distance to Grip Point | 30mm |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/KA06MD-M.pdf>
See store item page for other formats.