

KA06MSA-M Cut Sheet



NITRA pneumatic gripper, angular, single acting, N.O., 6mm bore, 30 degrees open position, -10 degrees closed position, side mount grip, anodized aluminum body, M3 x 0.5 threaded port(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KA06MSA-M>

Technical Specifications

Brand	NITRA
Item	Gripper
Working Fluid	Pneumatic
Grip Type	Angular
Action Type	Single acting
Operation Mode	N.O.
Bore Diameter	6mm
Open Position	30 degrees
Closed Position	-10 degrees
Grip Mount Style	Side
Body Material	Anodized aluminum
Port Information	M3 x 0.5 threaded
Cycle Rate	180 cyc/min
Maximum Distance to Grip Point	30mm

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document