

# KMF318A Cut Sheet



Roxburgh EMI input filter, 230/460 VAC, 3-phase, 18A, panel mount, EMI/RFI filtering, 2-stage, drive rated, high performance, screw terminals. For use with 3-phase AC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/KMF318A>

## Technical Specifications

<b>Brand</b>	Roxburgh
<b>Item</b>	Input filter
<b>Filter Type</b>	EMI
<b>Filter Voltage Rating</b>	230/460 VAC
<b>Number of Input Phases</b>	3
<b>Amperage Rating</b>	18A
<b>On/Off Switch</b>	No
<b>Fused</b>	No

<b>Mounting</b>	Panel
<b>Filtering</b>	EMI/RFI
<b>Number of Filter Stages</b>	2
<b>SCCR Rating</b>	5kA SCCR
<b>Filter Application</b>	Drive rated
<b>Filter Performance Level</b>	High performance
<b>Connector Type</b>	Screw terminals
<b>For Use With</b>	3-phase AC drives

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E191581
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/KMF318A.pdf>  
See store item page for other formats.