

# L12II Cut Sheet



Fibox hinged enclosure window, 5.04 x 9.76in window, smoked polycarbonate, 5.04 x 9.76in frame, polycarbonate, RAL 7035 light gray, polyurethane gasket. For use with IP65 enclosures. Mounting hardware included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/L12II>

## Technical Specifications

Brand	Fibox
Item	Hinged enclosure window
Window Size	5.04 x 9.76in
Window Material	Smoked polycarbonate
Frame Size	5.04 x 9.76in
Frame Material	Polycarbonate
Color	RAL 7035 light gray
Gasket Type	Polyurethane
Cutout Size	3.66 x 8.39in
For Use With	IP65 enclosures
Includes	Mounting hardware

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/L12II.pdf>  
See store item page for other formats.