

# LCR-38P-0130-C5-C1 Cut Sheet



ProSense potentiometer linear position sensor, pivoting slide, 130mm stroke, 38mm diameter x 233mm body, rod eyes mount, 8mm DIN 43650 Form C.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LCR-38P-0130-C5-C1>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Linear position sensor
<b>Transducer Type</b>	Potentiometer
<b>Action</b>	Pivoting slide
<b>Stroke</b>	130mm
<b>Resistance</b>	5k ohm
<b>Head Material</b>	Stainless steel
<b>Housing Material</b>	Anodized aluminum
<b>Housing Size</b>	38mm diameter x 233mm body

<b>Sensor Resolution</b>	Infinite
<b>Linearity</b>	+/- 0.1%
<b>Switching Cycles</b>	100,000,000 cycles
<b>Mounting</b>	Rod eyes
<b>IP Rating</b>	IP65
<b>Connection</b>	8mm DIN 43650 Form C
<b>Number of Wires</b>	4
<b>Includes</b>	Pivoting rod eye joint, electrical connector

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/LCR-38P-0130-C5-C1.pdf>  
See store item page for other formats.