

LKEH-102FEPUL-R Cut Sheet



Patlite LED signal tower, (1) tier, 100mm diameter, red, permanent or flashing (60 fpm +/- 3 fpm) light function, (32) alarms, 24 VDC, PNP polarity, colored lens, 265.2mm body length, light gray, 360 degree viewing angle, base mount, IP53.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/LKEH-102FEPUL-R>

Technical Specifications

Brand	Patlite
Item	Signal tower
Bulb Type	LED
Number of Pre-Assembled Tiers	1
Diameter	100mm
Light Color(s)	Red
Light Function	Permanent or flashing (60 fpm +/- 3 fpm)
Number of Alarms	32
Voltage Rating	24 VDC
Polarity	PNP
Lens Type	Colored

Body Length	265.2mm
Body Color	Light gray
Body Material	AES plastic
Tower Viewing Angle	360 degree
Loudness Decibel	105 dB at 1m
Tone Frequency	293 Hz
Tone Type	(32) selectable
Touch to Acknowledge	No
Connector Type	Pigtail
Mounting	Base
IP Rating	IP53

Agency Approvals

UL Listed File #	E215660
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	NONE
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/LKEH-102FEPUL-R.pdf>
See store item page for other formats.