

M.250-22Z-1224 Cut Sheet



Schmersal heavy duty limit switch, side rotary lever with metal belt roller, (2) N.O./ (2) N.C. contact(s), snap action, 122mm hole spacing, cast iron, (2) M25 x 1.5 cable entry.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/M.250-22Z-1224>

Technical Specifications

Brand	Schmersal
Item	Limit switch
Application	Belt alignment
Switch Type	Heavy duty
Actuator Type	Side rotary lever with metal belt roller
Contact Type	(2) N.O./ (2) N.C.
Action	Snap action
Reset	No
Body Width	103mm
Mounting Hole Spacing	122mm
Material	Cast iron
IP Rating	IP65 IP66 IP67
Operating Temperature	-20 degrees to 60 degrees C
Connection	(2) M25 x 1.5 cable entry

Agency Approvals

UL Listed File #	E57648
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/M.250-22Z-1224.pdf>
See store item page for other formats.