

M2430HPLSL Cut Sheet



AttaBox MachoBox series enclosure, NEMA 1/3/3R/4/4X/12/13, 24 x 30 x 10in (HxWxD), fiberglass reinforced polyester, Pantone 428 C glacier gray, single-door, slotted twist-lock latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/M2430HPLSL>

Technical Specifications

| | |
|---------------------------------|------------------------------|
| Brand | AttaBox |
| Item | Enclosure |
| Series | MachoBox |
| Subpanel | Purchase subpanel separately |
| Slope Top | No |
| NEMA Rating | 1/3/3R/4/4X/12/13 |
| IP Rating | IP66 |
| Nominal Enclosure Height | 24in |
| Nominal Enclosure Width | 30in |
| Nominal Enclosure Depth | 10in |
| Integral Mounting Feet | Yes |

| | |
|------------------------------------|-------------------------------------|
| Integral Mounting Flange | No |
| Dual Access | No |
| Knockouts | No |
| Material | Fiberglass reinforced polyester |
| Color | Pantone 428 C glacier gray |
| Cover Type | Single-door |
| Latch Type | Slotted twist-lock latch |
| Number Of Latches | 1 |
| Secondary Latch Type | Stainless steel quick-release latch |
| Number Of Secondary Latches | 4 |
| Padlockable | Yes |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E64358 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/M2430HPLSL.pdf>
See store item page for other formats.