

# M3024HPLSL Cut Sheet



AttaBox MachoBox series enclosure, NEMA 1/3/3R/4/4X/12/13, 30 x 24 x 10in (HxWxD), fiberglass reinforced polyester, Pantone 428 C glacier gray, single-door, slotted twist-lock latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/M3024HPLSL>

## Technical Specifications

<b>Brand</b>	AttaBox
<b>Item</b>	Enclosure
<b>Series</b>	MachoBox
<b>Subpanel</b>	Purchase subpanel separately
<b>Slope Top</b>	No
<b>NEMA Rating</b>	1/3/3R/4/4X/12/13
<b>IP Rating</b>	IP66
<b>Nominal Enclosure Height</b>	30in
<b>Nominal Enclosure Width</b>	24in
<b>Nominal Enclosure Depth</b>	10in
<b>Integral Mounting Feet</b>	Yes

<b>Integral Mounting Flange</b>	No
<b>Dual Access</b>	No
<b>Knockouts</b>	No
<b>Material</b>	Fiberglass reinforced polyester
<b>Color</b>	Pantone 428 C glacier gray
<b>Cover Type</b>	Single-door
<b>Latch Type</b>	Slotted twist-lock latch
<b>Number Of Latches</b>	1
<b>Secondary Latch Type</b>	Stainless steel quick-release latch
<b>Number Of Secondary Latches</b>	6
<b>Padlockable</b>	Yes

## Agency Approvals

<b>UL Listed File #</b>	E64358
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/M3024HPLSL.pdf>  
See store item page for other formats.