

MD4-0212T-1 Cut Sheet

ViewMarq MD4 series industrial LED message display, 2 line x 12 characters, 1.5in, 2in and 4in, (2) serial and (1) Ethernet port for configuration and external message control, NEMA 4/12, indoor use only.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MD4-0212T-1>



Technical Specifications

Brand	ViewMarq
Item	Industrial LED message display
Series	MD4
Display Size	2 line x 12 characters
Display Type	Tri-color LED
Character Size	1.5in, 2in and 4in
Character Color	Red, amber and green
Character Type	Embedded string and numeric variables
Scrolling	Right, left, up and down
Recommended Maximum Viewable Distance	200ft
Communication Port and Connection Type(s)	<ul style="list-style-type: none">• (1) Ethernet 10/100Base-T (RJ45)• (1) RS-232 (RJ12)• (1) RS-485 (3-pin terminal)

Port Protocol(s)	<ul style="list-style-type: none">• Modbus TCP Server• Modbus RTU Slave• ASCII
Port Speed(s)	<ul style="list-style-type: none">• up to 38.4k baud• 10/100 Mbps
Housing Material	Extruded aluminum
Housing Rating	NEMA 4/12
Environmental Requirements	Indoor use only
Includes	Mounting hardware, cable glands and (1) Ethernet patch cable
Programming Software	MD-PGMSW configuration software v2.0 or later
UL Rating	UL 61010 rated

Agency Approvals

UL Listed File #	E139594
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/MD4-0212T-1.pdf>
See store item page for other formats.