

# MDR-AP-1F Cut Sheet



AutomationDirect magnetic proximity sensor, rectangular, 10.2 x 36.8 x 16mm body, polybutylene terephthalate housing, PNP, N.O. output, 60mm sensing distance, flush, 5 kHz switching frequency, IP67, 3-pin M8 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MDR-AP-1F>

## Technical Specifications

<b>Brand</b>	AutomationDirect
<b>Item</b>	Proximity sensor
<b>Sensor Type</b>	Magnetic
<b>Shape</b>	Rectangular
<b>Housing Size</b>	10.2 x 36.8 x 16mm body
<b>Housing Material</b>	Polybutylene terephthalate
<b>Sensing Method</b>	Extended sensing
<b>Adjustable</b>	No
<b>Number of Wires</b>	3
<b>Switching Output</b>	PNP

<b>Operation Mode</b>	N.O. output
<b>Sensing Distance</b>	60mm
<b>Mounting Type</b>	Flush
<b>IO-Link Compatible</b>	No
<b>Switching Frequency</b>	5 kHz
<b>Operating Voltage</b>	10-30 VDC
<b>IP Rating</b>	IP67
<b>Connection</b>	3-pin M8 quick-disconnect
<b>Additional Information</b>	Purchase cable separately

## Agency Approvals

<b>UL Listed File #</b>	E328811
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/MDR-AP-1F.pdf>  
See store item page for other formats.