

# ME-402A-RYGB Cut Sheet



Patlite LED signal tower, (4) tiers, 25mm diameter, red/amber/green/blue, permanent light function, 24 VDC, NPN polarity, clear lens, 200mm body length, silver, 360 degree viewing angle, direct mount, IP42.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ME-402A-RYGB>

## Technical Specifications

<b>Brand</b>	Patlite
<b>Item</b>	Signal tower
<b>Bulb Type</b>	LED
<b>Number Of Tiers</b>	4
<b>Diameter</b>	25mm
<b>Light Color(s)</b>	Red/amber/green/blue
<b>Light Function</b>	Permanent
<b>Voltage Rating</b>	24 VDC
<b>Polarity</b>	NPN
<b>Lens Type</b>	Clear
<b>Body Length</b>	200mm
<b>Body Color</b>	Silver
<b>Body Material</b>	Aluminum
<b>Tower Viewing Angle</b>	360 degree
<b>Connector Type</b>	Pigtail
<b>Mounting</b>	Direct
<b>IP Rating</b>	IP42

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E215660
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	C22.2 No.14
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>