

MIF06 Cut Sheet



Roxburgh EMI input filter, 120/240 VAC, 1-phase, 6A, panel mount, EMI/RFI filtering, multi-stage, drive rated, very high performance, spring clamp terminals. For use with 1-phase AC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MIF06>

Technical Specifications

Brand	Roxburgh
Item	Input filter
Filter Type	EMI
Filter Voltage Rating	120/240 VAC
Number of Input Phases	1
Amperage Rating	6A
On/Off Switch	No
Fused	No

Mounting	Panel
Filtering	EMI/RFI
Number of Filter Stages	Multi
SCCR Rating	5kA SCCR
Filter Application	Drive rated
Filter Performance Level	Very high performance
Connector Type	Spring clamp terminals
For Use With	1-phase AC drives

Agency Approvals

UL Listed File #	None
UL Recognized File #	E191581
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/MIF06.pdf>
See store item page for other formats.