


MIV10 Cut Sheet



Fibox DIN rail, unslotted, 35 mm width, 7 mm height, 3.94in length, galvanized steel. Package of 1. For use with ULPCM100xxx ULPCM125xxx and ULPCM150xxxMNX series enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MIV10>

Technical Specifications

Brand	Fibox
Item	DIN rail
DIN Rail Type	Unslotted
Width	35 mm
Height	7 mm
Length	3.94in
Material	Galvanized steel
Quantity per Pack	1
For Use With	ULPCM100xxx ULPCM125xxx and ULPCM150xxxMNX series enclosures

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/MIV10.pdf>
See store item page for other formats.