

MMC-H-131107 Cut Sheet



IDEM safety switch set, non-contact coded magnetic, right exit mount, (2) N.C. safety output(s), (1) N.O. monitoring output(s), 316 stainless steel housing, 36 x 26mm, pigtail, 32.8ft/10m cable length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MMC-H-131107>

Technical Specifications

Brand	IDEM
Item	Safety switch set
Actuator Type	Non-contact coded magnetic
Mounting	Right exit
Safety Output Type	(2) N.C.
Monitoring Output Type	(1) N.O.
IP Rating	IP67 IP69K
Indicating Type	LED indication
Housing Material	316 stainless steel
Housing Size	36 x 26mm
Connection	Pigtail
Conductor Size	24 AWG
Cable Length	32.8ft/10m

Agency Approvals

UL Listed File #	E300466
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/MMC-H-131107.pdf>
See store item page for other formats.