

MPS-102C-R Cut Sheet



Patlite LED signal tower, (1) tier, 30mm diameter, red, permanent light function, 24 VDC, NPN/PNP polarity, colored lens, 68mm body length, silver, 360 degree viewing angle, direct mount, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MPS-102C-R>

Technical Specifications

| | |
|----------------------------|----------------------------|
| Brand | Patlite |
| Item | Signal tower |
| Bulb Type | LED |
| Number Of Tiers | 1 |
| Diameter | 30mm |
| Light Color(s) | Red |
| Light Function | Permanent |
| Voltage Rating | 24 VDC |
| Polarity | NPN/PNP |
| Lens Type | Colored |
| Body Length | 68mm |
| Body Color | Silver |
| Body Material | ABS plastic |
| Tower Viewing Angle | 360 degree |
| Connector Type | 4-pin M12 quick-disconnect |
| Mounting | Direct |
| IP Rating | IP65 |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E215660 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |