

# MRP-6CB Cut Sheet



NITRA pneumatic or water valve manifold, polypropylene (PP), white, rectangular, 150 psi maximum operating pressure, (6) stations, (2) 1/4in female NPT inlet(s), (6) 1/8in female NPT outlet(s), standard hole spacing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MRP-6CB>

## Technical Specifications

|                                   |                           |
|-----------------------------------|---------------------------|
| <b>Brand</b>                      | NITRA                     |
| <b>Item</b>                       | Valve manifold            |
| <b>Working Fluid</b>              | Air or inert gas or water |
| <b>Material</b>                   | Polypropylene (PP)        |
| <b>Color</b>                      | White                     |
| <b>Shape</b>                      | Rectangular               |
| <b>Number of Stations</b>         | 6                         |
| <b>Maximum Operating Pressure</b> | 150 psi                   |
| <b>Inlet Port</b>                 | (2) 1/4in female NPT      |
| <b>Outlet Port</b>                | (6) 1/8in female NPT      |
| <b>Mounting Hole Spacing</b>      | Standard                  |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/MRP-6CB.pdf>  
See store item page for other formats.