

MRP-9CB Cut Sheet



NITRA pneumatic or water valve manifold, polypropylene (PP), white, rectangular, 150 psi maximum operating pressure, (9) stations, (2) 1/4in female NPT inlet(s), (9) 1/8in female NPT outlet(s), standard hole spacing.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MRP-9CB>

Technical Specifications

Brand	NITRA
Item	Valve manifold
Working Fluid	Air or inert gas or water
Material	Polypropylene (PP)
Color	White
Shape	Rectangular
Number of Stations	9
Maximum Operating Pressure	150 psi
Inlet Port	(2) 1/4in female NPT
Outlet Port	(9) 1/8in female NPT
Mounting Hole Spacing	Standard

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/MRP-9CB.pdf>
See store item page for other formats.