

MTSP-P33-3BD36 Cut Sheet



IronHorse MTS premium efficiency AC induction motor, washdown and inverter rated, 1/3hp, 3-phase, 208-230/460 VAC, 3600rpm, TEFC, NEMA 56C frame, 304 stainless steel, C-face/rigid base mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MTSP-P33-3BD36>

Technical Specifications

| | |
|--------------------------|-----------------------------|
| Brand | IronHorse |
| Item | Motor |
| Series | MTS |
| Efficiency Group | Premium efficiency |
| Efficiency | 72 |
| Voltage Type | AC |
| Motor Type | Induction |
| Motor Application | Washdown and inverter rated |
| Horsepower Rating | 1/3hp |
| Number of Phases | 3 |
| Voltage Rating | 208-230/460 VAC |
| Synchronous Speed | 3600rpm |
| Nameplate RPM | 3500rpm |
| Overload Type | None |
| Enclosure Type | TEFC |
| Shaft Type | Round with square key |

| | |
|---------------------------------|--------------------------------|
| Shaft Diameter | 5/8in |
| Shaft Material | 304 stainless steel |
| Motor Frame | NEMA 56C |
| Frame Material | 304 stainless steel |
| Electrically Reversible | Yes |
| Insulation Class | Class F |
| IP Rating | IP69K |
| Constant Torque Rating | 10:1 |
| Variable Torque Rating | 20:1 |
| Service Factor | 1.15 |
| Integrated Brake | No |
| NEMA Design | Design B |
| Junction Box Orientation | F1 |
| Mounting | C-face/rigid base |
| Mounting Orientation | Horizontal or vertical |
| Additional Information | Class I Div 2 hazardous rating |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E517327 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | 602259 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/MTSP-P33-3BD36.pdf>
See store item page for other formats.