

MVE-00-0E Cut Sheet



AutomationDirect photoelectric sensor, tubular, threaded, plastic housing, through-beam emitter, infrared, 16m sensing distance, 20-253 VAC operating voltage, 2-wire, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MVE-00-0E>

Technical Specifications

| | |
|-------------------------------|----------------------------|
| Brand | AutomationDirect |
| Item | Photoelectric sensor |
| Shape | Tubular |
| Barrel Type | Threaded |
| Housing Size | 18mm diameter x 80mm body |
| IP Rating | IP67 |
| Housing Material | Plastic |
| Sensing Method | Through-beam emitter |
| Operating Voltage | 20-253 VAC |
| Number of Wires | 2 |
| Sensing Distance | 16m |
| Switching Frequency | 25 Hz |
| Light Emission (NP) | Infrared |
| Connection | 4-pin M12 quick-disconnect |
| Additional Information | Purchase cable separately |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E130644 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |