

MVR-A0-0A Cut Sheet



AutomationDirect photoelectric sensor, tubular, threaded, plastic housing, through-beam receiver, 16m sensing distance, 20-253 VAC operating voltage, dark-on, 3-wire, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/MVR-A0-0A>

Technical Specifications

Brand	AutomationDirect	Operating Voltage	20-253 VAC
Item	Photoelectric sensor	Number of Wires	3
Shape	Tubular	Sensing Distance	16m
Barrel Type	Threaded	Operation Mode	Dark-on
Housing Size	18mm diameter x 80mm body	Switching Frequency	25 Hz
IP Rating	IP67	Cable Length	6.5ft/2m
Housing Material	Plastic	Connection	Pigtail
Sensing Method	Through-beam receiver	Conductor Size	22 AWG

Agency Approvals

UL Listed File #	None
UL Recognized File #	E130644
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document