

# N12727220 Cut Sheet



Wiegmann enclosure, NEMA 12, 72 x 72 x 20in (HxWxD), floor mount, carbon steel, ANSI 61 gray, powder coat finish, double-door, 3-point keylocking/padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N12727220>

## Technical Specifications

|                                 |                              |
|---------------------------------|------------------------------|
| <b>Brand</b>                    | Wiegmann                     |
| <b>Item</b>                     | Enclosure                    |
| <b>Subpanel</b>                 | Purchase subpanel separately |
| <b>Slope Top</b>                | No                           |
| <b>NEMA Rating</b>              | 12                           |
| <b>Nominal Enclosure Height</b> | 72in                         |
| <b>Nominal Enclosure Width</b>  | 72in                         |
| <b>Nominal Enclosure Depth</b>  | 20in                         |
| <b>Mounting</b>                 | Floor                        |
| <b>Dual Access</b>              | No                           |

|                                  |  |
|----------------------------------|--|
| <b>Knockouts</b>                 | No   |
| <b>Material</b>                  | Carbon steel                               |
| <b>Color</b>                     | ANSI 61 gray                               |
| <b>Finish</b>                    | Powder coat                                |
| <b>Cover Type</b>                | Double-door                                |
| <b>Hinge Type</b>                | Continuous hinge                           |
| <b>Number of Hinges Per Door</b> | 1  |
| <b>Latch Type</b>                | 3-point keylocking/padlocking combo handle |
| <b>Padlockable</b>               | Yes  |
| <b>Keylocking</b>                | Yes  |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E64791                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/N12727220.pdf>  
See store item page for other formats.