

N412202208CDSSA Cut Sheet



Wiegmann Ultimate series disconnect enclosure, NEMA 4/4X/12/13, right flange, 20 x 22 x 8in (HxWxD), wall mount, 316L stainless steel, No. 3 intermediate polished finish, single-door, 2-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N412202208CDSSA>

Technical Specifications

Brand	Wiegmann	Knockouts	No
Item	Disconnect enclosure	Material	316L stainless steel
Series	Ultimate	Finish	No. 3 intermediate polished
Slope Top	No	Cover Type	Single-door
NEMA Rating	4/4X/12/13	Hinge Type	Concealed hinges
IP Rating	IP66	Number of Hinges Per Door	2
Disconnect Mounting	Right flange	Latch Type	2-point padlocking handle
Nominal Enclosure Dimensions	20 x 22 x 8in (HxWxD)	Subpanel	Purchase subpanel separately
Enclosure Height	20.00in	For Use With	Most major brand disconnect switches and circuit breakers
Enclosure Width	22.00in	Additional Information	Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier
Enclosure Depth	8.87in		
Mounting	Wall		
Integral Mounting Feet	No		
Integral Mounting Flange	No		

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document