

N412241608SS3PTC Cut Sheet



Wiegmann Ultimate series enclosure, NEMA 4X/12/13, 24 x 16 x 8in (HxWxD), wall mount, 304 stainless steel, No. 3 intermediate polished finish, single-door, 3-point 316L padlocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N412241608SS3PTC>

Technical Specifications

Brand	Wiegmann	Integral Mounting Feet	No
Item	Enclosure	Integral Mounting Flange	No
Series	Ultimate	Dual Access	No
Subpanel	Purchase subpanel separately	Knockouts	No
Slope Top	No	Material	304 stainless steel
NEMA Rating	4X/12/13	Finish	No. 3 intermediate polished
IP Rating	IP66	Cover Type	Single-door
Nominal Enclosure Dimensions	24 x 16 x 8in (HxWxD)	Hinge Type	Concealed hinges
Enclosure Height	24.00in	Number of Hinges Per Door	2
Enclosure Width	16.00in	Latch Type	3-point 316L padlocking handle
Enclosure Depth	8.92in	Padlockable	Yes
Mounting	Wall	Keylocking	No

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document