

# N412242006WSSC Cut Sheet



Wiegmann Ultimate series enclosure, NEMA 4/4X/12/13, 24 x 20 x 6in (HxWxD), wall mount, 304 stainless steel, No. 3 intermediate polished finish, single-door, 1/4-turn semi-flush oil-tight latch, polycarbonate window.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N412242006WSSC>

## Technical Specifications

|                          |                              |
|--------------------------|------------------------------|
| Brand                    | Wiegmann                     |
| Item                     | Enclosure                    |
| Series                   | Ultimate                     |
| Subpanel                 | Purchase subpanel separately |
| Slope Top                | No                           |
| NEMA Rating              | 4/4X/12/13                   |
| IP Rating                | IP66                         |
| Nominal Enclosure Height | 24in                         |
| Nominal Enclosure Width  | 20in                         |
| Nominal Enclosure Depth  | 6in                          |
| Mounting                 | Wall                         |
| Integral Mounting Feet   | No                           |

|                           |                                     |
|---------------------------|-------------------------------------|
| Integral Mounting Flange  | No                                  |
| Dual Access               | No                                  |
| Knockouts                 | No                                  |
| Material                  | 304 stainless steel                 |
| Finish                    | No. 3 intermediate polished         |
| Cover Type                | Single-door                         |
| Hinge Type                | Concealed hinges                    |
| Number of Hinges Per Door | 2                                   |
| Latch Type                | 1/4-turn semi-flush oil-tight latch |
| Window Material           | Polycarbonate                       |
| Padlockable               | No                                  |
| Keylocking                | No                                  |

## Agency Approvals

|                      |                                        |
|----------------------|----------------------------------------|
| UL Listed File #     | E64791                                 |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/N412242006WSSC.pdf>  
See store item page for other formats.