

# N412302408SSA3PTC Cut Sheet



Wiegmann Ultimate series enclosure, NEMA 4X/12/13, 30 x 24 x 8in (HxWxD), wall mount, 316L stainless steel, No. 3 intermediate polished finish, single-door, 3-point 316L padlocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N412302408SSA3PTC>

## Technical Specifications

|                          |                              |
|--------------------------|------------------------------|
| Brand                    | Wiegmann                     |
| Item                     | Enclosure                    |
| Series                   | Ultimate                     |
| Subpanel                 | Purchase subpanel separately |
| Slope Top                | No                           |
| NEMA Rating              | 4X/12/13                     |
| IP Rating                | IP66                         |
| Nominal Enclosure Height | 30in                         |
| Nominal Enclosure Width  | 24in                         |
| Nominal Enclosure Depth  | 8in                          |
| Mounting                 | Wall                         |
| Integral Mounting Feet   | No                           |

|                           |                                |
|---------------------------|--------------------------------|
| Integral Mounting Flange  | No                             |
| Dual Access               | No                             |
| Knockouts                 | No                             |
| Material                  | 316L stainless steel           |
| Finish                    | No. 3 intermediate polished    |
| Cover Type                | Single-door                    |
| Hinge Type                | Concealed hinges               |
| Number of Hinges Per Door | 2                              |
| Latch Type                | 3-point 316L padlocking handle |
| Padlockable               | Yes                            |
| Keylocking                | No                             |

## Agency Approvals

|                      |                                        |
|----------------------|----------------------------------------|
| UL Listed File #     | E64791                                 |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/N412302408SSA3PTC.pdf>  
See store item page for other formats.