

# N412423212CSTD Cut Sheet



Wiegmann Ultimate series disconnect enclosure, slope top, NEMA 4/12/13, right flange, 42 x 32 x 12in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, 3-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N412423212CSTD>

## Technical Specifications

|                          |                      |
|--------------------------|----------------------|
| Brand                    | Wiegmann             |
| Item                     | Disconnect enclosure |
| Series                   | Ultimate             |
| Slope Top                | Yes                  |
| NEMA Rating              | 4/12/13              |
| IP Rating                | IP66                 |
| Disconnect Mounting      | Right flange         |
| Nominal Enclosure Height | 46.87in              |
| Nominal Enclosure Width  | 32in                 |
| Nominal Enclosure Depth  | 12.89in              |
| Mounting                 | Wall                 |
| Integral Mounting Feet   | No                   |

|                           |                                                                                                                   |
|---------------------------|-------------------------------------------------------------------------------------------------------------------|
| Material                  | Carbon steel                                                                                                      |
| Color                     | ANSI 61 gray                                                                                                      |
| Finish                    | Powder coat                                                                                                       |
| Cover Type                | Single-door                                                                                                       |
| Hinge Type                | Concealed hinges                                                                                                  |
| Number of Hinges Per Door | 3                                                                                                                 |
| Latch Type                | 3-point padlocking handle                                                                                         |
| Subpanel                  | Purchase subpanel separately                                                                                      |
| Additional Information    | Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier |

## Agency Approvals

|                      |                                        |
|----------------------|----------------------------------------|
| UL Listed File #     | E64791                                 |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/N412423212CSTD.pdf>  
See store item page for other formats.