

N4241606 Cut Sheet



Wiegmann enclosure, NEMA 4/12/13, 24 x 16 x 6in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, (5) stainless steel clamps, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N4241606>

Technical Specifications

Brand	Wiegmann	Dual Access	No
Item	Enclosure	Knockouts	No
Subpanel	Purchase subpanel separately	Material	Carbon steel
Slope Top	No	Color	ANSI 61 gray
NEMA Rating	4/12/13	Finish	Powder coat
IP Rating	IP66	Cover Type	Single-door
Nominal Enclosure Height	24in	Hinge Type	Continuous hinge
Nominal Enclosure Width	16in	Number of Hinges Per Door	1
Nominal Enclosure Depth	6in	Latch Type	(5) stainless steel clamps
Mounting	Wall	Padlock Attachment Type	Padlock hasp and staple
Integral Mounting Feet	Yes	Padlockable	Yes
Integral Mounting Flange	No	Keylocking	No

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/N4241606.pdf>
See store item page for other formats.