


N4S723724FSSS Cut Sheet



Wiegmann enclosure, NEMA 3/4/4X/12, 72 x 37 x 24in (HxWxD), freestanding, 304 stainless steel, No. 3 intermediate polished finish, single-door, (9) stainless steel clamps, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/N4S723724FSSS>

Technical Specifications

Brand	Wiegmann
Item	Enclosure
Subpanel	Purchase subpanel separately
Slope Top	No
NEMA Rating	3/4/4X/12
Nominal Enclosure Height	72in
Nominal Enclosure Width	37in
Nominal Enclosure Depth	24in
Mounting	Freestanding
Dual Access	No

Knockouts	No
Material	304 stainless steel
Finish	No. 3 intermediate polished
Cover Type	Single-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	(9) stainless steel clamps
Padlock Attachment Type	Padlock hasp and staple
Padlockable	Yes
Keylocking	No

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/N4S723724FSSS.pdf>
See store item page for other formats.