

NIL20-036.000-SL Cut Sheet



PBC Simplicity 60 Plus series linear precision ground round shaft, 1060 steel, RC60-65, 8-12Ra, 1-1/4in diameter, 36in length. For use with 1-1/4in PBC bearings.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/NIL20-036.000-SL>

Technical Specifications

| | |
|-----------------------|-------------------------------|
| Brand | PBC |
| Item | Shaft |
| Series | Simplicity 60 Plus |
| Shaft Type | Linear precision ground round |
| Material | 1060 steel |
| Hardness | RC60-65 |
| Surface Finish | 8-12Ra |
| Diameter | 1-1/4in |
| Length | 36in |
| For Use With | 1-1/4in PBC bearings |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/NIL20-036.000-SL.pdf>
See store item page for other formats.