

NIL20SS-024.000-SL Cut Sheet



PBC Simplicity 60 Plus series linear precision ground round shaft, 440C stainless steel, RC50-55, 8-12Ra, 1-1/4in diameter, 24in length. For use with 1-1/4in PBC bearings.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/NIL20SS-024.000-SL>

Technical Specifications

Brand	PBC
Item	Shaft
Series	Simplicity 60 Plus
Shaft Type	Linear precision ground round
Material	440C stainless steel
Hardness	RC50-55
Surface Finish	8-12Ra
Diameter	1-1/4in
Length	24in
For Use With	1-1/4in PBC bearings

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/NIL20SS-024.000-SL.pdf>
See store item page for other formats.