


# NSB10 Cut Sheet



PBC linear shaft support, standard profile, anodized aluminum, 1in center height. For use with 5/8in diameter PBC shafts.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/NSB10>

---

## Technical Specifications

<b>Brand</b>	PBC
<b>Item</b>	Linear shaft support
<b>Profile</b>	Standard
<b>Material</b>	Anodized aluminum
<b>Center Height</b>	1in
<b>For Use With</b>	5/8in diameter PBC shafts

---

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

---

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/NSB10.pdf>  
See store item page for other formats.