

# OPT2407 Cut Sheet

WenglorTPL M-EBAR machine vision lighting, bar light, infrared light emission, 500mm luminous field, 545 x 47.6 x 45mm housing, 21.6-30 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/OPT2407>

## Technical Specifications

<b>Brand</b>	WenglorTPL
<b>Series</b>	M-EBAR
<b>Item</b>	Machine vision lighting
<b>Light Type</b>	Bar light
<b>Light emission</b>	Infrared
<b>Color Wavelength</b>	850 nm
<b>Beam Angle</b>	Plus or minus 7 degrees
<b>Luminous Field</b>	500mm
<b>Housing Size</b>	545 x 47.6 x 45mm
<b>Body Material</b>	Aluminium and fiberglass reinforced ABS

<b>Operation Mode</b>	Continuous and strobe
<b>Overdrive</b>	Yes
<b>Operating Voltage</b>	21.6-30 VDC
<b>Power Rating</b>	28.8W
<b>Current Consumption Continuous</b>	1.2A
<b>Current Consumption Strobe</b>	4.8A
<b>IP Rating</b>	IP65
<b>Connection</b>	5-pin M12 quick-disconnect

## Agency Approvals

<b>UL Listed File #</b>	E189727
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/OPT2407.pdf>  
See store item page for other formats.